

# F1A-NMNR-6-P

---

FSJ1-50A SureFlex® Jumper with interface types N Male and N Male  
Right Angle, 6 ft



## Product Classification

|                       |                               |
|-----------------------|-------------------------------|
| <b>Product Type</b>   | SureFlex® Premium, static PIM |
| <b>Product Series</b> | FSJ1-50A                      |

## General Specifications

|   |             |
|---|-------------|
| <b>Body Style, Connector A</b>            | Straight    |
| <b>Body Style, Connector B</b>            | Right angle |
| <b>Interface, Connector A</b>             | N Male      |
| <b>Interface, Connector B</b>             | N Male      |
| <b>Specification Sheet Revision Level</b> | A           |

## Dimensions

|                     |                    |
|---------------------|--------------------|
| <b>Length</b>       | 1.829 m   6.001 ft |
| <b>Nominal Size</b> | 1/4 in             |

## Electrical Specifications

|   |                      |
|---|----------------------|
| <b>3rd Order IMD Static</b>             | -107 dBm             |
| <b>3rd Order IMD Static Test Method</b> | Two +43 dBm carriers |

## VSWR/Return Loss

| Frequency Band | VSWR  | Return Loss (dB) |
|----------------|-------|------------------|
| 698–960 MHz    | 1.152 | 23.02            |
| 1700–2200 MHz  | 1.152 | 23.02            |
| 2200–2700 MHz  | 1.152 | 23.02            |

## Jumper Assembly Sample Label

# F1A-NMNR-6-P



## Environmental Specifications

### Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015



### Classification

Designed, manufactured and/or distributed under this quality management system

## Included Products

- |            |   |  |
|------------|---|--|
| 35422-33   | - | Heat Treated FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE Jacket  |
| 35422-75   | - | Heat Treated FSJ1RK-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated, fire retardant polyolefin jacket            |
| FSJ1-50A   | - | FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket   |
| FSJ1RK-50A | - | FSJ1-50A, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated, fire retardant polyolefin jacket, B2ca s1a d0 a1 Compliant |