

F1A-QMRNR-10

FSJ1-50A SureFlex® Jumper with interface types QMA Male Right Angle and N Male Right Angle, 10 ft



Product Classification

Product Type SureFlex® standard

Product Series FSJ1-50A

General Specifications

Body Style, Connector A Right angle

Body Style, Connector B Right angle

Interface, Connector A QMA Male

Interface, Connector B N Male

Dimensions

Length 3.048 m | 10 ft

Nominal Size 1/4 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.44	15

Jumper Assembly Sample Label

F1A-QMRNR-10



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system



Included Products

- FSJ1-50A – FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket