F4A-HPHMDM-10M-SGW



HELIAX® 1/2" SureFlex® Jumper with interface types 4.3-10 Male and 7-16 DIN Male with HELIAX® SureGuard weatherproofing, 10 m

- If there are threads along the entire device port length, the HELIAX® SureGuard weatherproofing solutions will only seal properly if the HSG-M29-ADPT adapter is installed on the device port
- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type SureFlex® HP, HELIAX® performance

Product Brand HELIAX® | SureFlex®

Product Series RSJ4-50

General Specifications

Body Style, Connector AStraightBody Style, Connector BStraightInterface, Connector A4.3-10 MaleInterface, Connector B7-16 DIN Male

Specification Sheet Revision Level

Dimensions

Length 10 m | 32.808 ft

Nominal Size 1/2 in

Electrical Specifications

3rd Order IMD Static Test Method Two +43 dBm carriers

 3rd Order IMD, typical
 -116 dBm

 DTF, Connector A
 -34 dB

 DTF, Connector B
 -34 dB

VSWR/Return Loss

Frequency Band VSWR, typical Return Loss, typical (dB)

698–960 MHz 1.101 26.36 **1700–2200 MHz** 1.101 26.36

ANDREW® an Amphenol company

F4A-HPHMDM-10M-SGW

2200–2700 MHz 1.106 25.96 **3400–3800 MHz** 1.222 20.01

Jumper Assembly Sample Label



Environmental Specifications

Immersion Test MethodMeets IEC 60529:2001, IP68 in mated condition

Weatherproofing Method HELIAX® SureGuard weatherproofing boot

Packaging and Weights

Included Weatherproofing boot

Regulatory Compliance/Certifications

Agency	С	lassification
--------	---	---------------

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant UK-ROHS Compliant



