

H4-NMNM-40-P

HL4-50™ Jumper with interface types N male and N type male, 40 ft



- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type	Cable assembly, plenum
Product Series	HL4-50A

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	N Male
Interface, Connector B	N Male
Specification Sheet Revision Level	A

Dimensions

Length	12.192 m 40 ft
Nominal Size	1/2 in

Electrical Specifications

3rd Order IMD Dynamic Test Method	Two +43 dBm carriers per IEC 62037
3rd Order IMD Static	-112 dBm
DTF, Connector A	-34 dB
DTF, Connector B	-34 dB

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
800–960 MHz	1.25	19.08
1700–2200 MHz	1.25	19.08
2500–2700 MHz	1.25	19.08

H4-NMNM-40-P

Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

