

MPC-NCNC130230F-SS



MPO Trunk Cable, Multimode, MPO to MPO, Aqua, 230 ft

Product Classification

Regional Availability	Latin America North America
Portfolio	NETCONNECT®
Product Type	Fiber trunk cable assembly
Product Brand	MPOptimate®
Product Series	MPC

General Specifications

Color, boot A	Black
Color, boot B	Black
Color, connector A	Aqua
Color, connector B	Beige
Connector A, quantity	1
Connector B, quantity	1
Interface, Connector A	MPO-12/UPC Female
Interface Feature, connector A	Unpinned
Interface, Connector B	MPO-12/UPC Female
Interface Feature, connector B	Unpinned
Jacket Color	Aqua
Total Fibers, quantity	12

Dimensions

Cord Length	70.1 m 229.987 ft
--------------------	---------------------

Optical Specifications

Fiber Mode	Multimode
-------------------	-----------

MPC-NCNC130230F-SS

Fiber Type OM3

Environmental Specifications

Environmental Space Plenum

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

Classification

Above maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant/Exempted

