



RJ45 Patch Cord, category 5e, 8-port, trans SL boot, blue, 10 ft

OBSOLETE

This product was discontinued on: May 1, 2018

Replaced By:

C0155D2 CommScope® Cat 5e U/UTP RJ45 Patch Cord, Non-Plenum

Product Classification

| | |
|-----------------------|-------------------------------------|
| Regional Availability | Asia Australia/New Zealand EMEA |
| Portfolio | NETCONNECT® |
| Product Type | Twisted pair patch cord |

General Specifications

| | |
|------------------------|--------------------|
| ANSI/TIA Category | 5e |
| Cable Type | U/UTP (unshielded) |
| Conductor Type | Stranded |
| Interface, Connector A | RJ45 plug |
| Interface, Connector B | RJ45 plug |
| Jacket Color | Blue |
| Pairs, quantity | 4 |
| Wiring | T568A |

Dimensions

| | |
|--------------------------------------|--------------------|
| Cord Length | 3.05 m 10.007 ft |
| Compatible Conductor Gauge, stranded | 24 AWG |

Environmental Specifications

| | |
|-----------------------|--------------------------------------|
| Operating Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Environmental Space | Non-plenum |
| Flammability Rating | CM |

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

