1-2055025-5 | OCJ-S2-15MASHA-S2



Fiber Optic Patch Cord, Simplex, Singlemode, SC/APC to SC/APC, yellow, 15 m

Product Classification

Regional Availability EMEA

Product Type Fiber patch cord, simplex

Product Series OCJ

General Specifications

Connector A, quantity

Color, boot AGreenColor, connector AGreenConnector B, quantity1

Color, boot B Green
Color, connector B Green
Interface, Connector A SC/APC
Interface, Connector B SC/APC
Jacket Color Yellow

Total Fibers, quantity 1

Dimensions


 Cord Length
 15 m | 49.213 ft

 Diameter Over Jacket
 1.8 mm | 0.071 in

Ordering Tree



1-2055025-5 | OCJ-S2-15MASHA-S2



Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A1, TeraSPEED®

Performance Grade Standard C grade

Insertion Loss, maximum, connector A 0.5 dB
Insertion Loss, maximum, connector B 0.5 dB
Return Loss, minimum, connector A 60 dB
Return Loss, minimum, connector B 60 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Environmental Space Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Packaging quantity

COMMSCOPE®

1-2055025-5 | OCJ-S2-15MASHA-S2

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Performance Grade Guarantee to meet IEC 61755-1 Random Mating requirement

