1-2105027-2



Fiber Optic Patch Cord, OM3, LC/LC duplex, 1.8 mm LSZH & OFNR, 12 m, aqua

Product Classification

| Regional Availability | Asia Australia/New Zealand China India | |
|------------------------|----------------------------------------------|--|
| Portfolio | CommScope® | |
| Product Type | Fiber patch cord, duplex | |
| Product Series | 210 | |
| General Specifications | | |
| Connector A, quantity | 2 | |
| Color, boot A | Beige | |
| Color, connector A | Beige | |
| Connector B, quantity | 2 | |
| Color, boot B | Beige | |
| Color, connector B | Beige | |
| Interface, Connector A | LC/UPC | |
| Interface, Connector B | LC/UPC | |
| Jacket Color | Aqua | |
| Polarity | Pairs, flipped | |
| Total Fibers, quantity | 2 | |
| Dimensions | | |
| Cord Length | 12 m 39.37 ft | |
| Diameter Over Jacket | 1.8 mm 0.071 in | |
| Ordering Tree | | |

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 26, 2024



| to 9 | - | 2105027 | - | 0 to 9 |
|------|--------|-----------------------|---|--------|
| E | xample | s of Lengths (meters) | | |
| -5 | | 5 meters | | |
| 10 | D | 10 meters | | |
| 1! | 5 | 15 meters | | |
| 79 | 9 | 79 meters | | |
| 81 | y | Specific length | | |
| 91 | V | Specific length | | |

Optical Specifications

| Fiber Mode | Multimode |
|--------------------------------------|-----------------|
| Fiber Type | OM3, LazrSPEED® |
| Insertion Loss, maximum, connector A | 0.3 dB |
| Insertion Loss, maximum, connector B | 0.3 dB |
| Return Loss, minimum, connector A | 20 dB |
| Return Loss, minimum, connector B | 20 dB |

Environmental Specifications

| Environmental Space | Dual Rated LSZH/Riser |
|-------------------------|---------------------------------------------------|
| Qualification Standards | IEC 60332-1 IEC 60332-3 IEC 60754 IEC 61034 |

Packaging and Weights

Packaging quantity

1


Regulatory Compliance/Certifications

| Agency | Classification |
|------------|-----------------------------------------------------------------------|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 26, 2024







Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 26, 2024

