1471522 | FPM-07/7-AT034M-39/25



Fiber Optic Patch Cord, Multi-fiber, Singlemode, 24 fibers, SC/UPC to SC/UPC, yellow, 34 m

Product Classification

Regional AvailabilityLatin America| North AmericaProduct TypeFiber distribution cable assembly

Product Series FPM

General Specifications

Connector A, quantity 24
Color, boot A Blue
Color, connector A Blue
Connector B, quantity 24
Color, boot B Blue
Color, connector B Blue

Construction Type Stranded
Interface, Connector A SC/UPC
Interface, Connector B SC/UPC
Jacket Color Yellow
Total Fibers, quantity 24

Dimensions

Breakout Length, connector A990.6 mm | 39 inBreakout Length, connector B635 mm | 25 inCord Length34 m | 111.549 ft

Optical Specifications

Fiber Mode Singlemode

Fiber Type OS2
Insertion Loss, maximum, connector A 0.2 dB

COMMSCOPE®

1471522 | FPM-07/7-AT034M-39/25

Insertion Loss, maximum, connector B0.2 dBReturn Loss, minimum, connector A57 dBReturn Loss, minimum, connector B57 dB

Environmental Specifications

Environmental Space Plenum

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

