



RJ45 Patch Cord, category 5e, 8-port, trans SL boot, blue, 1 ft

OBSOLETE

This product was discontinued on: May 1, 2018

Replaced By:

C0155D2 CommScope® Cat 5e U/UTP RJ45 Patch Cord, Non-Plenum

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	5e
Cable Type	U/UTP (unshielded)
Conductor Type	Stranded
Interface, Connector A	RJ45 plug
Interface, Connector B	RJ45 plug
Jacket Color	Blue
Pairs, quantity	4
Wiring	T568A

Dimensions

Cord Length	0.31 m 1.017 ft
Diameter Over Jacket	5.4 mm 0.213 in
Compatible Conductor Gauge, stranded	24 AWG

Mechanical Specifications

Plug Insertion Life, minimum750 times

Environmental Specifications

Operating Temperature-20 °C to +60 °C (-4 °F to +140 °F)

Environmental SpaceNon-plenum

Flammability RatingCM

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

