

# C400-NMNF-1M

---

CNT-400 CNT® Jumper with interface types N Male and N Female, 1 m



## Product Classification

|                       |                        |
|-----------------------|------------------------|
| <b>Product Type</b>   | Braided cable assembly |
| <b>Product Brand</b>  | CNT®                   |
| <b>Product Series</b> | CNT-400                |

## General Specifications

|   |          |
|---|----------|
| <b>Body Style, Connector A</b>            | Straight |
| <b>Body Style, Connector B</b>            | Straight |
| <b>Cable Family</b>                       | CNT-400  |
| <b>Interface, Connector A</b>             | N Male   |
| <b>Interface, Connector B</b>             | N Female |
| <b>Specification Sheet Revision Level</b> | A        |

## Dimensions

|                     |                |
|---------------------|----------------|
| <b>Length</b>       | 1 m   3.281 ft |
| <b>Nominal Size</b> | 0.400 in       |

## VSWR/Return Loss

| Frequency Band | VSWR  | Return Loss (dB) |
|----------------|-------|------------------|
| 700–2000 MHz   | 1.222 | 20.01            |
| 2000–3000 MHz  | 1.288 | 18               |

## Jumper Assembly Sample Label

# C400-NMNF-1M



## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015



### Classification

Designed, manufactured and/or distributed under this quality management system

## Included Products

- 400BPNF-C – Type N Female for CNT-400 braided cable
- 400BPNM-C – Type N Male for CNT-400 braided cable
- CNT-400 – CNT-400, CNT® 50 Ohm Braided Coaxial Cable, variable, black PE jacket