F4A-HPNMNM-1M

HELIAX® 1/2" SureFlex® Jumper with interface types N Male and N Male, 1 m

Product Classification

1700-2200 MHz

2200-2700 MHz

Product Type	SureFlex® HP, HELIAX® p	SureFlex® HP, HELIAX® performance	
Product Brand	HELIAX® SureFlex®	HELIAX® SureFlex®	
Product Series	RSJ4-50		
General Specifications			
Body Style, Connector A	Straight		
Body Style, Connector B	Straight		
Interface, Connector A	N Male		
Interface, Connector B	N Male		
Specification Sheet Revision Level	А		
Dimensions			
Length	1 m 3.281 ft		
Nominal Size	1/2 in		
Electrical Specifications			
3rd Order IMD Static Test Method	Two +43 dBm carriers		
3rd Order IMD, typical	-112 dBm		
DTF, Connector A	-34 dB		
DTF, Connector B	-34 dB		
VSWR/Return Loss			
Frequency Band	VSWR, typical	Return Loss, typical (dB)	
680-960 MHz	1.065	30.04	

1.065

1.106

30.04

25.96

Page 1 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 18, 2025

F4A-HPNMNM-1M

Jumper Assembly Sample Label



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant
UK-ROHS	Compliant



Page 2 of 2

