



RJ45 Patch Cord, category 6A, shielded, black, 10 ft

OBSOLETE

This product was discontinued on: May 1, 2018

Replaced By:

NPC6ASVDB

NPC RJ45 Patch Cord, category 6A, Shielded, CM (PVC)

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	6A
Cable Type	F/UTP (shielded)
Conductor Type	Stranded
Interface, Connector A	RJ45 plug
Interface, Connector B	RJ45 plug
Jacket Color	Black
Pairs, quantity	4
Wiring	T568B

Dimensions

Cord Length	3.05 m 10.007 ft
Diameter Over Jacket	6 mm 0.236 in
Compatible Conductor Gauge, stranded	26 AWG

Material Specifications

Conductor Material Tin plated copper

Environmental Specifications

Operating Temperature -20 °C to +60 °C (-4 °F to +140 °F)
Storage Temperature -20 °C to +80 °C (-4 °F to +176 °F)
Environmental Space Non-plenum
Flammability Rating CM

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant/Exempted

