



RJ45 Patch Cord, category 6, UTP, blue SL boot, blue, 20 m

**OBSOLETE**

This product was discontinued on: May 1, 2018

**Replaced By:**

NPC06UVDB

NETCONNECT® Cat 6 U/UTP RJ45 Patch Cord, Non-Plenum

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	6
Cable Type	U/UTP (unshielded)
Conductor Type	Stranded
Interface, Connector A	RJ45 plug
Interface, Connector B	RJ45 plug
Jacket Color	Blue
Pairs, quantity	4
Wiring	T568B

Dimensions

Cord Length	20 m   65.617 ft
Compatible Conductor Gauge, stranded	24 AWG

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Environmental Specifications

Operating Temperature -20 °C to +60 °C (-4 °F to +140 °F)  
Environmental Space Non-plenum  
Flammability Rating CM

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

