

PTS1P-HMHM-10-P

PTS1-50-P SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male, 10 ft



- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type	SureFlex® Premium, static PIM
Product Series	PTS1-50-P

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	4.3-10 Male
Specification Sheet Revision Level	A

Dimensions

Length	3.048 m 10 ft
Nominal Size	1/4 in

Electrical Specifications

3rd Order IMD	-110 dBm
3rd Order IMD Test Method	Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.152	23.02
1700–2700 MHz	1.152	23.02

Jumper Assembly Sample Label

PTS1P-HMHM-10-P



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition