CC0877-000 | OCJ-L1-10MASHA-L1

Blue



Fiber Optic Patch Cord, Duplex, Singlemode, LC/UPC to LC/UPC, yellow, 10 m

Product Classification

Regional Availability FMFA

Product Type Fiber patch cord, duplex

Product Series OCJ

General Specifications

Connector A, quantity 2

Color, boot A Blue

Color, connector A 2 Connector B, quantity

Color, boot B Blue

Color, connector B Blue

Interface, Connector A LC/UPC

Interface, Connector B LC/UPC

Jacket Color Yellow

Total Fibers, quantity

Dimensions


Cable Assembly Length Range (m) 1 - 999Cable Assembly Length Range (ft) 1 - 999

Cord Length 10 m | 32.808 ft **Diameter Over Jacket** 1.8 mm | 0.071 in

Ordering Tree



CC0877-000 | OCJ-L1-10MASHA-L1



Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A1, TeraSPEED®

Performance Grade Standard C grade

Insertion Loss, maximum, connector A0.5 dBInsertion Loss, maximum, connector B0.5 dBReturn Loss, minimum, connector A50 dBReturn Loss, minimum, connector B50 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Environmental Space Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Packaging quantity



CC0877-000 | OCJ-L1-10MASHA-L1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



* Footnotes

Performance Grade Guarantee to meet IEC 61755-1 Random Mating requirement

