

F2A-PHMDR-5M

FSJ2-50 SureFlex® Jumper with interface types 4.3 -10 Male and 7-16 DIN Male Right Angle, 5 m



Product Classification

Product Type SureFlex® standard

Product Series FSJ2-50

General Specifications

Body Style, Connector A Straight

Body Style, Connector B Right angle

Interface, Connector A 4.3-10 Male

Interface, Connector B 7-16 DIN Male

Specification Sheet Revision Level A

Dimensions

Length 5 m | 16.404 ft

Nominal Size 3/8 in

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 700–3000 MHz | 1.44 | 15 |

Jumper Assembly Sample Label

F2A-PHMDR-5M



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |



Included Products

| | | |
|---------|---|---|
| FSJ2-50 | - | FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket |
|---------|---|---|