

# F2A-PNMNM-M5

---

FSJ2-50 SureFlex® Jumper with interface types N Male and N Male,  
0.5 m



## Product Classification

**Product Type** SureFlex® standard

**Product Series** FSJ2-50

## General Specifications

**Body Style, Connector A** Straight

**Body Style, Connector B** Straight

**Interface, Connector A** N Male

**Interface, Connector B** N Male

**Specification Sheet Revision Level** A

## Dimensions

**Length** 0.5 m | 1.64 ft

**Nominal Size** 3/8 in

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.23	20

## Jumper Assembly Sample Label

# F2A-PNMNM-M5



## Environmental Specifications

### Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system



## Included Products

- 35422-42 – Heat Treated FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket
- FSJ2-50 – FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket