F4A-HPHMDM-15M-SGW



HELIAX® 1/2" SureFlex® Jumper with interface types 4.3-10 Male and Din 7-16 Male with HELIAX® SureGuard weatherproofing, 15m

- If there are threads along the entire device port length, the HELIAX® SureGuard weatherproofing solutions will only seal properly if the HSG-M29-ADPT adapter is installed on the device port
- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type	SureFlex® HP, HELIAX® performance
Product Brand	HELIAX® SureFlex®
Product Series	RSJ4-50
General Specifications	
Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	7-16 DIN Male
Specification Sheet Revision Level	А
Dimensions	
Length	15 m 49.213 ft
Nominal Size	1/2 in
Electrical Specifications	
3rd Order IMD Static Test Method	Two +43 dBm carriers
3rd Order IMD, typical	-116 dBm
DTF, Connector A	-34 dB
DTF, Connector B	-34 dB
VSWR/Return Loss	
Francisco De est	

Frequency Band	VSWR, typical	Return Loss, typical (dB)
698–960 MHz	1.101	26.36
1700–2200 MHz	1.101	26.36

Page 1 of 2



F4A-HPHMDM-15M-SGW

2200–2700 MHz	1.106	25.96
3480–3800 MHz	1.222	20.01

Jumper Assembly Sample Label



Environmental Specifications

Immersion Test Method

Weatherproofing Method

Meets IEC 60529:2001, IP68 in mated condition HELIAX® SureGuard weatherproofing boot

Packaging and Weights

Included

Weatherproofing boot

Regulatory Compliance/Certifications

Agency

ISO 9001.2015

Classification

Designed, manufactured and/or distributed under this quality management system

©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 18, 2025

Page 2 of 2