



RJ45 Patch Cord, category 5e, FTP, white, LSZH, white boot, 3 m

OBSOLETE

This product was discontinued on: May 1, 2018

Replaced By:

C017772

Category 5e F/UTP Patch Cord, RJ45 to RJ45, 4-pair, LSZH

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	5e
Cable Type	F/UTP (shielded)
Conductor Type	Stranded
Interface, Connector A	RJ45 plug
Interface, Connector B	RJ45 plug
Jacket Color	White
Pairs, quantity	4
Wiring	T568B

Dimensions

Cord Length	3 m 9.843 ft
Diameter Over Jacket	5.3 mm 0.209 in
Compatible Conductor Gauge, stranded	26 AWG

Material Specifications

Conductor Material Bare copper

Environmental Specifications

Environmental Space Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

