



Copper Patch Cord, 4P AMP-TWIST, category 7A, S/FTP, LSZH, stranded, white, 1 m

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	7A
Cable Type	S/FTP (shielded)
Conductor Type	Stranded
Interface, Connector A	4P AMP-TWIST Plug
Interface, Connector B	4P AMP-TWIST plug
Jacket Color	White
Pairs, quantity	4

Dimensions

Cord Length	1 m 3.281 ft
Diameter Over Jacket	5.59 mm 0.22 in

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Environmental Space	Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

1711637-1

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

