



RJ45 Patch Cord, category 6, 8-port, trans SL boot, gray, 7 ft

OBSOLETE

This product was discontinued on: May 1, 2018

Replaced By:

NPC06UVDB

NETCONNECT® Cat 6 U/UTP RJ45 Patch Cord, Non-Plenum

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	6
Cable Type	U/UTP (unshielded)
Conductor Type	Stranded
Interface, Connector A	RJ45 plug
Interface, Connector B	RJ45 plug
Jacket Color	Gray
Pairs, quantity	4
Wiring	T568B

Dimensions

Cord Length	2.13 m 6.988 ft
Compatible Conductor Gauge, stranded	24 AWG

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Non-plenum
Flammability Rating	CM

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

