

F2A-HMHM-2-ATW1



FSJ2-50 SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male with HELIAX® SureGuard weatherproofing, 2 ft

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type Wireless transmission cable assembly

Product Series FSJ2-50

General Specifications

Body Style, Connector A Straight

Body Style, Connector B Straight

Interface, Connector A 4.3-10 Male

Interface, Connector B 4.3-10 Male

Specification Sheet Revision Level A

Dimensions

Length 0.61 m | 2.001 ft

Nominal Size 3/8 in

Electrical Specifications

3rd Order IMD Dynamic -118 dBm

3rd Order IMD Dynamic Test Method Two +43 dBm carriers per IEC 62037

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.2	21
1700–2700 MHz	1.2	21

Jumper Assembly Sample Label

