

# F4-DMDR-14M-SGW-D

---



D-CLASS HELIAX® 1/2" SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male Right Angle with HELIAX® SureGuard weatherproofing, 14 m

- If there are threads along the entire device port length, the HELIAX® SureGuard weatherproofing solutions will only seal properly if the HSG-M29-ADPT adapter is installed on the device port

## Product Classification

<b>Product Type</b>	SureFlex® D-CLASS, dynamic PIM
<b>Product Brand</b>	HELIAX®   SureFlex®
<b>Product Series</b>	RSJ4-50

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Right angle
<b>Interface, Connector A</b>	7-16 DIN Male
<b>Interface, Connector B</b>	7-16 DIN Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	14 m   45.932 ft
<b>Nominal Size</b>	1/2 in

## Electrical Specifications

<b>3rd Order IMD Dynamic</b>	-116 dBm
<b>3rd Order IMD Dynamic Test Method</b>	Two +43 dBm carriers per IEC 62037
<b>DTF, Connector A</b>	-34 dB
<b>DTF, Connector B</b>	-32 dB

## Logo Image

# F4-DMDR-14M-SGW-D



## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-960 MHz	1.101	26.36
1700-2200 MHz	1.101	26.36
2200-2700 MHz	1.173	21.98
3400-3800 MHz	1.222	20.01

## Jumper Assembly Sample Label

Batch Manufacturing Date (two digit year and week)  
Manufacturing Plant Product Revision

0123456789 US22 1240 /A

COMMSCOPE Andrew Solutions™  
**F4-DMDM-2M-D** Part Number  
2 M (6.562 FT)  
SUREFLEX ASSEMBLY  
U.S. PATENT 5802710  
Product of UNITED STATES  
12US220001242 Serial Number



# F4-DMDR-14M-SGW-D

---

## Environmental Specifications

<b>Immersion Test Method</b>	Meets IEC 60529:2001, IP68 in mated condition
<b>Weatherproofing Method</b>	HELIAX® SureGuard weatherproofing boot

## Packaging and Weights

<b>Included</b>	Weatherproofing boot
-----------------	----------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

