



RJ45 Patch Cord, category 6, LSZH, trans SL boot, gray, 2 m

OBSOLETE

This product was discontinued on: May 1, 2018

Replaced By:

NPC06UZDB

NETCONNECT® Cat 6 U/UTP RJ45 Patch Cord, LSZH

Product Classification

| | |
|-----------------------|-------------------------------------|
| Regional Availability | Asia Australia/New Zealand EMEA |
| Portfolio | NETCONNECT® |
| Product Type | Twisted pair patch cord |

General Specifications

| | |
|------------------------|--------------------|
| ANSI/TIA Category | 6 |
| Cable Type | U/UTP (unshielded) |
| Conductor Type | Stranded |
| Interface, Connector A | RJ45 plug |
| Interface, Connector B | RJ45 plug |
| Jacket Color | Gray |
| Pairs, quantity | 4 |
| Wiring | T568B |

Dimensions

| | |
|--------------------------------------|------------------|
| Cord Length | 2 m 6.562 ft |
| Diameter Over Jacket | 5.6 mm 0.22 in |
| Compatible Conductor Gauge, stranded | 24 AWG |

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Environmental Specifications

Operating Temperature -20 °C to +60 °C (-4 °F to +140 °F)

Environmental Space Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

