

F1A-HMHM-6-CC

FSJ1-50A SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male, 6 ft



- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type	Wireless transmission cable assembly
Product Brand	HELIAX® SureFlex®
Product Series	FSJ1-50A

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	4.3-10 Male
Specification Sheet Revision Level	A

Dimensions

Length	1.829 m 6.001 ft
Nominal Size	1/4 in

Electrical Specifications

3rd Order IMD Dynamic	-110 dBm
3rd Order IMD Dynamic Test Method	Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)	Insertion Loss (dB)
0-3000 MHz	1.135	23.98	
800-2700 MHz			0.8
3000-6000 MHz	1.222	20.01	

Jumper Assembly Sample Label

F1A-HMHM-6-CC



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system