

# L4A-PDMDR-1M5

---

LDF4-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male Right Angle, 1.5 m



## Product Classification

|                       |                    |
|-----------------------|--------------------|
| <b>Product Type</b>   | SureFlex® standard |
| <b>Product Series</b> | LDF4-50A           |

## General Specifications

|   |               |
|---|---------------|
| <b>Body Style, Connector A</b>            | Straight      |
| <b>Body Style, Connector B</b>            | Right angle   |
| <b>Interface, Connector A</b>             | 7-16 DIN Male |
| <b>Interface, Connector B</b>             | 7-16 DIN Male |
| <b>Specification Sheet Revision Level</b> | A             |

## Dimensions

|                     |                  |
|---------------------|------------------|
| <b>Length</b>       | 1.5 m   4.921 ft |
| <b>Nominal Size</b> | 1/2 in           |

## Electrical Specifications

|                         |        |
|-------------------------|--------|
| <b>DTF, Connector A</b> | -32 dB |
| <b>DTF, Connector B</b> | -32 dB |

## Jumper Assembly Sample Label

# L4A-PDMDR-1M5



## Environmental Specifications

### Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

## Included Products

LDF4-50A

- LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket (Halogen free jacketing non-fire-retardant)