



RJ45 Patch Cord, category 5e, F/UTP, white, 2.5 m

**OBSOLETE**

This product was discontinued on: May 1, 2018

**Replaced By:**

C017772                      Category 5e F/UTP Patch Cord, RJ45 to RJ45, 4-pair, LSZH

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	5e
Cable Type	F/UTP (shielded)
Conductor Type	Stranded
Interface, Connector A	RJ45 plug
Interface, Connector B	RJ45 plug
Jacket Color	White
Pairs, quantity	4

Dimensions

Cord Length	2.5 m   8.202 ft
Compatible Conductor Gauge, stranded	26 AWG

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Environmental Space	Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

