



RJ45 Consolidation Point Cable, plug to jack, S/FTP, white, 15 m

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	6A
Cable Type	S/FTP (shielded)
Interface, Connector A	RJ45 plug
Interface, Connector B	RJ45 jack
Jacket Color	White
Pairs, quantity	4

Dimensions

Cord Length	15 m 49.213 ft
Diameter Over Jacket	5.59 mm 0.22 in

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Environmental Space	Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

1-1711360-5

