



RJ45 Patch Cord, category 6A, S/FTP, red, 10 m

OBSOLETE

This product was discontinued on: May 1, 2018

Replaced By:

NPC6ASZDB

NETCONNECT® Cat 6A S/FTP RJ45 Patch Cord, LSZH

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	6A
Cable Type	S/FTP (shielded)
Conductor Type	Stranded
Interface, Connector A	RJ45 plug
Interface, Connector B	RJ45 plug
Jacket Color	Red
Pairs, quantity	4

Dimensions

Cord Length	10 m 32.808 ft
Diameter Over Jacket	5.59 mm 0.22 in
Compatible Conductor Gauge, stranded	26 AWG

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Environmental Space	Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

