



Copper Patch Cord, RJ45 to 4P AMP-TWIST plug, cat 6A, S/FTP, stranded, LSZH, white, 10 m

OBSOLETE
This product was discontinued on: September 25, 2022

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	6A
Cable Type	S/FTP (shielded)
Conductor Type	Stranded
Interface, Connector A	RJ45 plug
Interface, Connector B	4P AMP-TWIST Plug
Jacket Color	White
Pairs, quantity	4

Dimensions

Cord Length	10 m 32.808 ft
Diameter Over Jacket	5.9 mm 0.232 in
Compatible Conductor Gauge, stranded	26 AWG

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
-----------------------	-------------------------------------

Environmental Space

Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
RCM	Compliant to electrical safety & telecommunications requirements
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

