



RJ45 Patch Cord, category 6, 8-plug, trans SL boot, white, 9 ft

**OBSOLETE**

This product was discontinued on: May 1, 2018

**Replaced By:**

NPC06UVDB                      NETCONNECT® Cat 6 U/UTP RJ45 Patch Cord, Non-Plenum

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	6
Cable Type	U/UTP (unshielded)
Conductor Type	Stranded
Interface, Connector A	RJ45 plug
Interface, Connector B	RJ45 plug
Jacket Color	White
Pairs, quantity	4
Wiring	T568B

Dimensions

Cord Length	2.74 m   8.99 ft
Compatible Conductor Gauge, stranded	24 AWG

Mechanical Specifications

# 1859250-9

Plug Insertion Life, minimum	750 times
Environmental Specifications	
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Non-plenum
Flammability Rating	CM

## Packaging and Weights

Packaging quantity	1
--------------------	---

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

