



Fiber Optic Pigtail, Simplex, Singlemode, SC/UPC to Stub, 0.9 mm diameter, 3 m

Product Classification

Regional Availability	EMEA
Product Type	Fiber pigtail, jacketed
Product Series	OCP

General Specifications

Connector A, quantity	1
Color, boot A	Blue
Color, connector A	Blue
Interface, Connector A	SC/UPC
Jacket Color	Yellow
Total Fibers, quantity	1

Dimensions

Cord Length	3 m 9.843 ft
--------------------	----------------

Ordering Tree

CC2979-000 | OCP-S1-03MASEN-XX



Connector/adaptor type		
Standard C grade	Superior B grade	Type
S1	SF	SC/UPC
S2	SG	SC/APC 8°
S3	SH	SC/APC 9°
L1	LF	LC/UPC
L2	LG	LC/APC
-	EC	LSH/APC 8°

Cable type			Fiber type
ASEN	900 µm	Semi-tight jacket	A1
HSEN	900 µm	Semi-tight jacket	A2

Cable length	
02	2 meters

- Standard Configuration by default 900µm buffer
 buffer color : yellow
 250 µm color : natural or milky white

Optical Specifications

Fiber Mode Singlemode
Fiber Type G.657.A1, TeraSPEED®

Environmental Specifications

Environmental Space Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

