## F1A-HMHM-2M-P

# FSJ1-50A SureFlex® Jumper with interface types 4.3-10 Male and 4.3-

WARNING: DO NOT MATE WITH 4.1-9.5 DIN

#### **Product Classification**

**Product Type** SureFlex® Premium, static PIM

Product Brand HELIAX® | SureFlex®

**Product Series** FSJ1-50A

General Specifications

Body Style, Connector A Straight

Body Style, Connector B Straight

Interface, Connector A 4.3-10 Male

Interface, Connector B 4.3-10 Male

Specification Sheet Revision Level A

**Dimensions** 

**Length** 2 m | 6.562 ft

Nominal Size 1/4 in

**Electrical Specifications** 

**3rd Order IMD** -107 dBm

**3rd Order IMD Test Method** Two +43 dBm carriers

#### VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-960 MHz	1.152	23.02
1700-2200 MHz	1.152	23.02
2200-2700 MHz	1.152	23.02

### Jumper Assembly Sample Label





#### **Environmental Specifications**

**Immersion Test Method** 

Meets IEC 60529:2001, IP68 in mated condition

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant/Exempted

