

# L4R-HMDF-14M-D

---

D-CLASS LDF4RK-50A SureFlex® Jumper with interface types 4.3-10 Male and 7-16 DIN Female, 13 m; D-CLASS LDF4R-50A SureFlex® Jumper with interface types 4.3-10 Male and 7-16 DIN Female, 14 m



- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

## Product Classification

<b>Product Type</b>	SureFlex® D-CLASS, dynamic PIM
<b>Product Brand</b>	HELIAX®   SureFlex®
<b>Product Series</b>	LDF4-50A

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	4.3-10 Male
<b>Interface, Connector B</b>	7-16 DIN Female
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	14 m   45.932 ft
<b>Nominal Size</b>	1/2 in

## Logo Image

# L4R-HMDF-14M-D



## Electrical Specifications

<b>3rd Order IMD Dynamic</b>	-116 dBm
<b>3rd Order IMD Dynamic Test Method</b>	Two +43 dBm carriers per IEC 62037
<b>DTF, Connector A</b>	-34 dB
<b>DTF, Connector B</b>	-34 dB

## VSWR/Return Loss

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
<b>698–960 MHz</b>	1.101	26.36
<b>1700–2200 MHz</b>	1.101	26.36
<b>2200–2700 MHz</b>	1.135	23.98
<b>3400–3800 MHz</b>	1.222	20.01

## Jumper Assembly Sample Label

# L4R-HMDF-14M-D



## Environmental Specifications

<b>EN50575 CPR Cable EuroClass Fire Performance</b>	B2ca
<b>EN50575 CPR Cable EuroClass Smoke Rating</b>	s1a
<b>EN50575 CPR Cable EuroClass Droplets Rating</b>	d1
<b>EN50575 CPR Cable EuroClass Acidity Rating</b>	a1
<b>Immersion Test Method</b>	Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

