

Fiber Optic Pigtail, Multi-fiber, Singlemode, 12 fibers, SC/UPC to stub, 6.17 m

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber pigtail, multi-fiber
Product Series	FPM

General Specifications

Color, boot A	Blue
Color, connector A	Blue
Connector A, quantity	12
Construction Type	Stranded
Interface, Connector A	SC/UPC
Jacket Color	Yellow
Total Fibers, quantity	12

Dimensions

Cord Length	6.17 m 20.243 ft
--------------------	--------------------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum, connector A	0.2 dB
Return Loss, minimum, connector A	55 dB

Environmental Specifications

Environmental Space	Plenum
----------------------------	--------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

