



RJ45 Patch Cord, category 5e, 8-port, trans SL boot, gray, 5 ft

## OBSOLETE

This product was discontinued on: May 1, 2018

### Replaced By:

C0155D2

CommScope® Cat 5e U/UTP RJ45 Patch Cord, Non-Plenum

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA
<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Twisted pair patch cord

## General Specifications

<b>ANSI/TIA Category</b>	5e
<b>Cable Type</b>	U/UTP (unshielded)
<b>Conductor Type</b>	Stranded
<b>Interface, Connector A</b>	RJ45 plug
<b>Interface, Connector B</b>	RJ45 plug
<b>Jacket Color</b>	Gray
<b>Pairs, quantity</b>	4
<b>Wiring</b>	T568A

## Dimensions

<b>Cord Length</b>	4 m   13.123 ft
<b>Compatible Conductor Gauge, stranded</b>	24 AWG

# 1859238-5

---

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Environmental Space</b>	Non-plenum
<b>Flammability Rating</b>	CM

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

