



RJ45 Patch Cord, category 5e, 8-port, trans SL boot, black, 25 ft

**OBSOLETE**

This product was discontinued on: May 1, 2018

**Replaced By:**

C0155D2                      CommScope® Cat 5e U/UTP RJ45 Patch Cord, Non-Plenum

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	5e
Cable Type	U/UTP (unshielded)
Conductor Type	Stranded
Interface, Connector A	RJ45 plug
Interface, Connector B	RJ45 plug
Jacket Color	Black
Pairs, quantity	4
Wiring	T568A

Dimensions

Cord Length	7.62 m   25 ft
Diameter Over Jacket	5.4 mm   0.213 in
Compatible Conductor Gauge, stranded	24 AWG

Mechanical Specifications

**Plug Insertion Life, minimum** 750 times

Environmental Specifications

**Operating Temperature** -20 °C to +60 °C (-4 °F to +140 °F)

**Environmental Space** Non-plenum

**Flammability Rating** CM

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

