

# F4-DMDR-4M5-D

---

D-CLASS HELIAX® 1/2" SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male Right Angle, 4.5 M



## Product Classification

<b>Product Type</b>	SureFlex® D-CLASS, dynamic PIM
<b>Product Series</b>	RSJ4-50

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Right angle
<b>Interface, Connector A</b>	7-16 DIN Male
<b>Interface, Connector B</b>	7-16 DIN Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	4.5 m   14.764 ft
<b>Nominal Size</b>	1/2 in

## Electrical Specifications

<b>3rd Order IMD Dynamic</b>	-116 dBm
<b>3rd Order IMD Dynamic Test Method</b>	Two +43 dBm carriers per IEC 62037
<b>DTF, Connector A</b>	-34 dB
<b>DTF, Connector B</b>	-32 dB

## Logo Image

# F4-DMDR-4M5-D



## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-960 MHz	1.083	27.99
1700-2200 MHz	1.083	27.99
2200-2700 MHz	1.135	23.98
3400-3800 MHz	1.222	20.01

## Jumper Assembly Sample Label

Batch
Manufacturing Date (two digit year and week)

Manufacturing Plant
Product Revision

0123456789
US22
1240
/A

**COMMSCOPE** Andrew Solutions™  
**F4-DMDM-2M-D** ——— **Part Number**  
 2 M (6.562 FT)  
 SUREFLEX ASSEMBLY  
 U.S. PATENT 5802710  
 Product of UNITED STATES

12US220001242 ——— **Serial Number**



# F4-DMDR-4M5-D

---

## Environmental Specifications

**Immersion Test Method**

Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system

