



RJ45 Patch Cord, category 6, 8-port, trans SL boot, black, 17 ft

OBSOLETE

This product was discontinued on: May 1, 2018

Replaced By:

NPC06UVDB

NETCONNECT® Cat 6 U/UTP RJ45 Patch Cord, Non-Plenum

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	6
Cable Type	U/UTP (unshielded)
Conductor Type	Stranded
Interface, Connector A	RJ45 plug
Interface, Connector B	RJ45 plug
Jacket Color	Black
Pairs, quantity	4
Wiring	T568B

Dimensions

Cord Length	5.18 m 16.995 ft
Diameter Over Jacket	5.6 mm 0.22 in
Compatible Conductor Gauge, stranded	24 AWG

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Environmental Specifications

Operating Temperature -20 °C to +60 °C (-4 °F to +140 °F)

Environmental Space Non-plenum

Flammability Rating CM

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

