1471811 | FPM-07/K-AN050M-25/39



Fiber Optic Patch Cord, Multi-fiber, Singlemode, 4 fibers, SC/UPC to LC /UPC, yellow, 50 m

Product Classification

Regional AvailabilityLatin America| North AmericaProduct TypeFiber distribution cable assembly

Product Series FPM

General Specifications

Connector A, quantity

Color, boot A

Blue

Color, connector A

Connector B, quantity

Color, boot B

Blue

Color, connector B

Blue

Construction Type Stranded
Interface, Connector A LC/UPC
Interface, Connector B SC/UPC
Jacket Color Yellow
Total Fibers, quantity 4

Dimensions

Breakout Length, connector A635 mm | 25 inBreakout Length, connector B990.6 mm | 39 inCord Length50 m | 164.042 ft

Optical Specifications

Fiber Mode Singlemode

Fiber TypeOS2Insertion Loss, maximum, connector A0.3 dBInsertion Loss, maximum, connector B0.2 dB

Page 1 of 2

1471811 | FPM-07/K-AN050M-25/39

Return Loss, minimum, connector A55 dBReturn Loss, minimum, connector B55 dB

Environmental Specifications

Environmental Space Plenum

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

