



Fiber Optic Patch Cord, Multi-fiber, Singlemode, 24 fibers, SC/UPC to SC /UPC, 44 m

Product Classification

| | |
|-----------------------|-----------------------------------|
| Regional Availability | Latin America North America |
| Product Type | Fiber distribution cable assembly |
| Product Series | FPM |

General Specifications

| | |
|------------------------|----------|
| Connector A, quantity | 24 |
| Color, boot A | Blue |
| Color, connector A | Blue |
| Connector B, quantity | 24 |
| Color, boot B | Blue |
| Color, connector B | Blue |
| Construction Type | Stranded |
| Interface, Connector A | SC/UPC |
| Interface, Connector B | SC/UPC |
| Jacket Color | Yellow |
| Total Fibers, quantity | 24 |

Dimensions

| | |
|------------------------------|-------------------|
| Breakout Length, connector A | 990.6 mm 39 in |
| Breakout Length, connector B | 1524 mm 60 in |
| Cord Length | 44 m 144.357 ft |

Optical Specifications

| | |
|--------------------------------------|------------|
| Fiber Mode | Singlemode |
| Fiber Type | OS2 |
| Insertion Loss, maximum, connector A | 0.2 dB |

| | |
|--------------------------------------|--------|
| Insertion Loss, maximum, connector B | 0.2 dB |
| Return Loss, minimum, connector A | 57 dB |
| Return Loss, minimum, connector B | 57 dB |

Environmental Specifications

| | |
|---------------------|--------|
| Environmental Space | Plenum |
|---------------------|--------|

Packaging and Weights

| | |
|--------------------|---|
| Packaging quantity | 1 |
|--------------------|---|

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|---|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

