



RJ45 Patch Cord, category 6, UTP, LSZH, red, 3 m

**OBSOLETE**

This product was discontinued on: May 1, 2018

**Replaced By:**

NPC06UZDB

NETCONNECT® Cat 6 U/UTP RJ45 Patch Cord, LSZH

Product Classification

|                       |                                     |
|-----------------------|-------------------------------------|
| Regional Availability | Asia   Australia/New Zealand   EMEA |
| Portfolio             | NETCONNECT®                         |
| Product Type          | Twisted pair patch cord             |

General Specifications

|                        |                    |
|------------------------|--------------------|
| ANSI/TIA Category      | 6                  |
| Cable Type             | U/UTP (unshielded) |
| Conductor Type         | Stranded           |
| Interface, Connector A | RJ45 plug          |
| Interface, Connector B | RJ45 plug          |
| Jacket Color           | Red                |
| Pairs, quantity        | 4                  |

Dimensions

|                                      |                |
|--------------------------------------|----------------|
| Cord Length                          | 3 m   9.843 ft |
| Compatible Conductor Gauge, stranded | 24 AWG         |

Environmental Specifications

Environmental Space

Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

| Agency     | Classification                                                                                                                 |
|------------|--------------------------------------------------------------------------------------------------------------------------------|
| CHINA-ROHS | Below maximum concentration value                                                                                              |
| REACH-SVHC | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS       | Compliant                                                                                                                      |
| UK-ROHS    | Compliant                                                                                                                      |

