



Fiber Optic Patch Cord, OS2, SC/UPC-SC/UPC, 24F RBR, 2.0 mm subunits, 70 m, yellow, 25"/60" breakouts

Product Classification

|                       |                                   |
|-----------------------|-----------------------------------|
| Regional Availability | Latin America   North America     |
| Product Type          | Fiber distribution cable assembly |
| Product Series        | FPM                               |

General Specifications

|                        |          |
|------------------------|----------|
| Connector A, quantity  | 24       |
| Color, boot A          | Blue     |
| Color, connector A     | Blue     |
| Connector B, quantity  | 24       |
| Color, boot B          | Blue     |
| Color, connector B     | Blue     |
| Construction Type      | Stranded |
| Interface, Connector A | SC/UPC   |
| Interface, Connector B | SC/UPC   |
| Jacket Color           | Yellow   |
| Total Fibers, quantity | 24       |

Dimensions

|                              |                   |
|------------------------------|-------------------|
| Breakout Length, connector A | 635 mm   25 in    |
| Breakout Length, connector B | 1524 mm   60 in   |
| Cord Length                  | 70 m   229.659 ft |

Optical Specifications

|                                      |            |
|--------------------------------------|------------|
| Fiber Mode                           | Singlemode |
| Fiber Type                           | OS2        |
| Insertion Loss, maximum, connector A | 0.2 dB     |

|                                      |        |
|--------------------------------------|--------|
| Insertion Loss, maximum, connector B | 0.2 dB |
| Return Loss, minimum, connector A    | 57 dB  |
| Return Loss, minimum, connector B    | 57 dB  |

Environmental Specifications

|                     |        |
|---------------------|--------|
| Environmental Space | Plenum |
|---------------------|--------|

Packaging and Weights

|                    |   |
|--------------------|---|
| Packaging quantity | 1 |
|--------------------|---|

Regulatory Compliance/Certifications

| Agency     | Classification  |
|------------|---|
| CHINA-ROHS | Above maximum concentration value   |
| REACH-SVHC | Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS       | Compliant/Exempted  |
| UK-ROHS    | Compliant/Exempted  |

