



Fiber Optic Pigtail, Simplex, Singlemode, SC/UPC to Stub, 0.9 mm diameter, multicolor, 1.5 m

Product Classification

Regional Availability	Asia
Product Type	Fiber pigtail, jacketed
Product Series	OCP

General Specifications

Connector A, quantity	12
Color, boot A	Blue
Color, connector A	Blue
Interface, Connector A	SC/UPC
Total Fibers, quantity	12

Dimensions

Cord Length	1.5 m 4.921 ft
--------------------	------------------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A1, TeraSPEED®

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency

CHINA-ROHS
ISO 9001:2015
REACH-SVHC
ROHS
UK-ROHS

Classification

Below maximum concentration value
Designed, manufactured and/or distributed under this quality management system
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant
Compliant

