



Fiber Optic Pigtail, 12 color kit, Singlemode, SC/APC to Stub, 0.9 mm diameter, 1.5 m

## Product Classification

Regional Availability	Asia
Product Type	Fiber pigtail, jacketed
Product Series	OCP

## General Specifications

Connector A, quantity	12
Color, boot A	Green
Color, connector A	Green
Interface, Connector A	SC/APC
Total Fibers, quantity	12

## Dimensions

Cord Length	1.5 m   4.921 ft
Diameter Over Jacket	0.9 mm   0.035 in

## Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A1

## Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
---------------------	-------------------------------

## Packaging and Weights

Packaging quantity	12
--------------------	----

## Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

