

F1A-PNRNR-M5

FSJ1-50A SureFlex® Jumper with interface types N Male Right Angle and N Male Right Angle, 0.5 m



Product Classification

Product Type SureFlex® standard

Product Series FSJ1-50A

General Specifications

Body Style, Connector A Right angle

Body Style, Connector B Right angle

Interface, Connector A N Male

Interface, Connector B N Male

Orientation 0°

Specification Sheet Revision Level A

Dimensions

Length 0.5 m | 1.64 ft

Nominal Size 1/4 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.29	18

Jumper Assembly Sample Label

F1A-PNRNR-M5



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

- FSJ1-50A – FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket