

# F2-HMHM-1M-D



D-CLASS FSJ2-50 SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male, 1 m

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

## Product Classification

Product Type	SureFlex® D-CLASS, dynamic PIM
Product Brand	HELIAX®   SureFlex®
Product Series	FSJ2-50

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	4.3-10 Male
Specification Sheet Revision Level	A

## Dimensions

Length	1 m   3.281 ft
Nominal Size	3/8 in

## Logo Image

# F2-HMHM-1M-D



## Electrical Specifications

3rd Order IMD Dynamic	-119 dBm
3rd Order IMD Dynamic Test Method	Two +43 dBm carriers per IEC 62037

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.101	26.36
1700–2200 MHz	1.101	26.36
2500–2700 MHz	1.101	26.36

## Jumper Assembly Sample Label

# F2-HMHM-1M-D



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system