

F2A-HMHM-25-ATW1



FSJ2-50 SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male with HELIAX® SureGuard weatherproofing, 25 ft

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type Wireless transmission cable assembly

Product Series FSJ2-50

General Specifications

Body Style, Connector A Straight

Body Style, Connector B Straight

Interface, Connector A 4.3-10 Male

Interface, Connector B 4.3-10 Male

Specification Sheet Revision Level A

Dimensions

Length 7.62 m | 25 ft

Nominal Size 3/8 in

Electrical Specifications

3rd Order IMD Dynamic -118 dBm

3rd Order IMD Dynamic Test Method Two +43 dBm carriers per IEC 62037

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.2	21
1700–2700 MHz	1.2	21

Jumper Assembly Sample Label

F2A-HMHM-25-ATW1



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

