

F2P43A-PDMDM-3M

FSJ2P-50 SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 3 m



Product Classification

Product Type	Wireless transmission cable assembly
Product Series	FSJ2-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Male
Specification Sheet Revision Level	A

Dimensions

Length	3 m 9.843 ft
Nominal Size	3/8 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
680–806 MHz	1.15	23.13
806–960 MHz	1.13	24.29
1427–1535 MHz	1.13	24.29
1700–2300 MHz	1.15	23.13
2535–2655 MHz	1.26	19.08
3400–3800 MHz	1.26	19.08

Jumper Assembly Sample Label

F2P43A-PDMDM-3M



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

